

BD FACSAria Fusion: Instrument Configuration				
Laser	Parameter Name	Longpass Dichroic Filter	Bandpass Filter	Detector
355nm	BUV 396	NA	379/28	C
	BUV 496	450LP	515/30	B
	BUV 737	690LP	740/35	A

405nm	BV421	410LP	450/50	F
	BV510	505LP	525/50	E
	BV605	600LP	610/20	D
	BV650	635LP	670/30	C
	BV711	690LP	710/50	B
	BV786	750LP	780/60	A

488nm	SSC	NA	488/10	C
	FITC	505LP	530/30	B
	PERCP-CY5.5	690LP	710/50	A

561nm	PE	570LP	586/15	D
	PE-CF594	600LP	610/20	C
	PE-CY5	650LP	670/30	B
	PE-CY7	750LP	780/60	A

637nm	APC	650LP	670/30	C
	A700	690LP	710/50	B
	APC-CY7	750LP	780/60	A